





FOCAL LENGTH (EFL): 200 ± 2

BACK FOCAL LENGTH (BFL): 197,35

- 1 266nm Laser AR Coating
R(ABS) < 0,25% @ 266nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 95,218 CX Øe 11,7 λ SEE NOTE 1 3/ 2 (0,2) $\lambda=632,8$ nm 4/ - 5/ 10 - 5 6/ $3\text{J}\cdot\text{cm}^{-2}$; 266nm; 20ns [20Hz]		GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 λ SEE NOTE 1 3/ 2 (0,2) $\lambda=632,8$ nm 4/ 2,18' 5/ 10 - 5 6/ $3\text{J}\cdot\text{cm}^{-2}$; 266nm; 20ns [20Hz]	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE $\lambda = 355\text{nm}$ SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® 12,7mm Dia x 200mm FL, 266nm Laser AR Coating, 3J Coated, Plano-Convex Lens 38666	
		DWG NO	SHEET SIZE A4	SHEET 1 OF 1