



NOTES:

- 1. SUBSTRATE:  
H-K51
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: MgF2 (400-700nm)  
R(AVG) ≤ 1.75% @ 400 - 700nm

- 3. CENTERING: ≤30 ARCMIN



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONVEX
SURFACE QUALITY	80-50 (typical)	80-50 (typical)
CLEAR APERTURE	Ø 31.41	Ø 31.41
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

EFL @ 587.6nm	21.60
BFL @ 587.6nm	11
THIRD ANGLE PROJECTION	
ALL DIMS IN	mm

TITLE	34.9mm Dia. x 21.6mm FL, MgF2 Coated, Aspheric Condenser Lens
DWG NO	21201
	SHEET 1 OF 1