




FOCAL LENGTH (EFL): $-18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $-19,95$

1 AR COATING: YAG-BBAR
 $R(\text{abs}) < 0.25\% @ 532\text{nm}$
 $R(\text{abs}) < 0.25\% @ 1064\text{nm}$
 $R(\text{avg}) < 1.0\% @ 500 - 1100\text{nm}$

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 14,12±0,014 CV Øe 11 3/ 3 (0,5) $\lambda=632,8 \text{ nm}$ 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF11 785/258	R ∞ PL Øe 11 3/ 3 (0,5) $\lambda=632,8 \text{ nm}$ 4/ 1,27' 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE		LENS PCV 12 X -18 YAGBBAR TS			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm		DWG NO		21312		SHEET SIZE A4	SHEET 1 OF 1
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING										
INDICATIONS IN ACCORDANCE WITH ISO 10110										