






FOCAL LENGTH (EFL): $-40 \pm 0,4$
 BACK FOCAL LENGTH (BFL): $-42,31$

1 AR COATING: YAG-BBAR
 $R(\text{abs}) < 0.25\% @ 532\text{nm}$
 $R(\text{abs}) < 0.25\% @ 1064\text{nm}$
 $R(\text{avg}) < 1.0\% @ 500 - 1100\text{nm}$

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 20,67±0,021 CV Øe 19 3/ 3 (0,5) $\lambda=632,8 \text{ nm}$ 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BK7 517/642	R ∞ PL Øe 19 3/ 3 (0,5) $\lambda=632,8 \text{ nm}$ 4/ 1,93' 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	LENS PCV 20 X -40 YAGBBAR TS		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	21316	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm				