

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0 Revision Date: 10/17/2017 SDS Number: 838796-00009 Date of last issue: 05/02/2017
Date of first issue: 11/26/2014

SECTION 1. IDENTIFICATION

Product name : MOLYKOTE™ 112 High Performance Lube/ Sealant
Product code : 02651114

Manufacturer or supplier's details

Company Identification : THE DOW CHEMICAL COMPANY
2030 WILLARD H DOW CENTER
MIDLAND MI 48674-0000
UNITED STATES

Telephone : 800-258-2436

24-Hour Emergency Contact : Chemtrec +1 800-424-9300

Local Emergency Number : 800-424-9300

E-mail address : SDSQuestion@dow.com

Recommended use of the chemical and restrictions on use

Recommended use : Lubricants and lubricant additives

SECTION 2. HAZARDS IDENTIFICATION

GHS classification in accordance with 29 CFR 1910.1200

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture
Chemical nature : Silicone grease

Hazardous ingredients

Chemical name	CAS-No.	Concentration (% w/w)
Methylphenyl Siloxane modified Silica	Not Assigned	$\geq 5 - < 10$
Dimethyl Siloxane reaction with Silica	67762-90-7	$\geq 1 - < 5$

SECTION 4. FIRST AID MEASURES

If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version	Revision Date:	SDS Number:	Date of last issue: 05/02/2017
5.0	10/17/2017	838796-00009	Date of first issue: 11/26/2014

- | | |
|---|---|
| In case of skin contact | : Wash with water and soap as a precaution.
Get medical attention if symptoms occur. |
| In case of eye contact | : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists. |
| If swallowed | : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water. |
| Most important symptoms and effects, both acute and delayed | : None known. |
| Protection of first-aiders | : No special precautions are necessary for first aid responders. |
| Notes to physician | : Treat symptomatically and supportively. |

SECTION 5. FIRE-FIGHTING MEASURES

- | | |
|--|---|
| Suitable extinguishing media | : Water spray
Alcohol-resistant foam
Carbon dioxide (CO ₂)
Dry chemical |
| Unsuitable extinguishing media | : None known. |
| Specific hazards during fire fighting | : Exposure to combustion products may be a hazard to health. |
| Hazardous combustion products | : Carbon oxides
Silicon oxides
Formaldehyde |
| Specific extinguishing methods | : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area. |
| Special protective equipment for fire-fighters | : Wear self-contained breathing apparatus for firefighting if necessary.
Use personal protective equipment. |

SECTION 6. ACCIDENTAL RELEASE MEASURES

- | | |
|---|--|
| Personal precautions, protective equipment and emergency procedures | : Follow safe handling advice and personal protective equipment recommendations. |
|---|--|

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version	Revision Date:	SDS Number:	Date of last issue: 05/02/2017
5.0	10/17/2017	838796-00009	Date of first issue: 11/26/2014

- Environmental precautions : Discharge into the environment must be avoided.
Prevent further leakage or spillage if safe to do so.
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material.
For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

SECTION 7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice.
Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labeled containers.
Store in accordance with the particular national regulations.
- Materials to avoid : Do not store with the following product types:
Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredients with workplace control parameters

Ingredients	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Methylphenyl Siloxane modified Silica	Not Assigned	TWA (Dust)	20 Million particles per cubic foot (Silica)	OSHA Z-3
		TWA (Dust)	80 mg/m3 / %SiO2	OSHA Z-3

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0 Revision Date: 10/17/2017 SDS Number: 838796-00009 Date of last issue: 05/02/2017
Date of first issue: 11/26/2014

			(Silica)	
Dimethyl Siloxane reaction with Silica	67762-90-7	TWA (Dust)	20 Million particles per cubic foot (Silica)	OSHA Z-3
		TWA (Dust)	80 mg/m3 / %SiO2 (Silica)	OSHA Z-3

These substance(s) are inextricably bound in the product and therefore do not contribute to a dust inhalation hazard.

II Dimethyl Siloxane reaction with Silica

Engineering measures : Processing may form hazardous compounds (see section 10).
Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : General and local exhaust ventilation is recommended to maintain vapor exposures below recommended limits. Where concentrations are above recommended limits or are unknown, appropriate respiratory protection should be worn. Follow OSHA respirator regulations (29 CFR 1910.134) and use NIOSH/MSHA approved respirators. Protection provided by air purifying respirators against exposure to any hazardous chemical is limited. Use a positive pressure air supplied respirator if there is any potential for uncontrolled release, exposure levels are unknown, or any other circumstance where air purifying respirators may not provide adequate protection.

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
Safety glasses

Skin and body protection : Skin should be washed after contact.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.
These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0	Revision Date: 10/17/2017	SDS Number: 838796-00009	Date of last issue: 05/02/2017 Date of first issue: 11/26/2014
----------------	------------------------------	-----------------------------	---

Appearance	: Grease
Color	: off-white
Odor	: none
Odor Threshold	: No data available
pH	: Not applicable
Melting point/freezing point	: No data available
Initial boiling point and boiling range	: Not applicable
Flash point	: > 101 °C Method: closed cup
Evaporation rate	: Not applicable
Flammability (solid, gas)	: Not classified as a flammability hazard
Self-ignition	: The substance or mixture is not classified as pyrophoric. The substance or mixture is not classified as self heating.
Upper explosion limit / Upper flammability limit	: No data available
Lower explosion limit / Lower flammability limit	: No data available
Vapor pressure	: Not applicable
Relative vapor density	: No data available
Relative density	: 1.1
Solubility(ies) Water solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Autoignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity Viscosity, dynamic	: Not applicable
Explosive properties	: Not explosive
Oxidizing properties	: The substance or mixture is not classified as oxidizing.

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0	Revision Date: 10/17/2017	SDS Number: 838796-00009	Date of last issue: 05/02/2017 Date of first issue: 11/26/2014
----------------	------------------------------	-----------------------------	---

Molecular weight : No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : Not classified as a reactivity hazard.

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : Use at elevated temperatures may form highly hazardous compounds.
Can react with strong oxidizing agents.
Hazardous decomposition products will be formed at elevated temperatures.

Conditions to avoid : None known.

Incompatible materials : Oxidizing agents

Hazardous decomposition products

Thermal decomposition : Benzene
Formaldehyde

SECTION 11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Ingredients:

Methylphenyl Siloxane modified Silica:

Acute oral toxicity	: LD50 (Rat): > 5,000 mg/kg Assessment: The substance or mixture has no acute oral toxicity Remarks: Based on data from similar materials
Acute inhalation toxicity	: Assessment: The substance or mixture has no acute inhalation toxicity Remarks: Based on data from similar materials
Acute dermal toxicity	: Assessment: The substance or mixture has no acute dermal toxicity Remarks: Based on data from similar materials

Skin corrosion/irritation

Not classified based on available information.

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version	Revision Date:	SDS Number:	Date of last issue: 05/02/2017
5.0	10/17/2017	838796-00009	Date of first issue: 11/26/2014

Ingredients:

Methylphenyl Siloxane modified Silica:

Species: Rabbit
Result: No skin irritation
Remarks: Based on data from similar materials

Serious eye damage/eye irritation

Not classified based on available information.

Ingredients:

Methylphenyl Siloxane modified Silica:

Species: Rabbit
Result: No eye irritation
Remarks: Based on data from similar materials

Respiratory or skin sensitization

Skin sensitization

Not classified based on available information.

Respiratory sensitization

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Ingredients:

Methylphenyl Siloxane modified Silica:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: Based on data from similar materials

Carcinogenicity

Not classified based on available information.

IARC No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0	Revision Date: 10/17/2017	SDS Number: 838796-00009	Date of last issue: 05/02/2017 Date of first issue: 11/26/2014
----------------	------------------------------	-----------------------------	---

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Ingredients:

Methylphenyl Siloxane modified Silica:

Ecotoxicology Assessment

Acute aquatic toxicity : This product has no known ecotoxicological effects.

Persistence and degradability

No data available

Bioaccumulative potential

No data available

Mobility in soil

No data available

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Resource Conservation and Recovery Act (RCRA) : This product has been evaluated for RCRA characteristics and does not meet the criteria of hazardous waste if discarded in its purchased form.

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.

SECTION 14. TRANSPORT INFORMATION

International Regulations

UNRTDG

Not regulated as a dangerous good

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0 Revision Date: 10/17/2017 SDS Number: 838796-00009 Date of last issue: 05/02/2017
Date of first issue: 11/26/2014

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

Domestic regulation

49 CFR

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know

CERCLA Reportable Quantity

Ingredients	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
Toluene	108-88-3	1000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 302 Extremely Hazardous Substances Threshold Planning Quantity

This material does not contain any components with a section 302 EHS TPQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

US State Regulations

Pennsylvania Right To Know

Dimethyl siloxane, trimethylsiloxy-terminated	63148-62-9
Methylphenyl Siloxane modified Silica	Not Assigned
Dimethyl Siloxane reaction with Silica	67762-90-7
Toluene	108-88-3

California Prop. 65

WARNING: This product can expose you to chemicals including Toluene, which is/are known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

California Permissible Exposure Limits for Chemical Contaminants

Methylphenyl Siloxane modified Silica	Not Assigned
---------------------------------------	--------------

The ingredients of this product are reported in the following inventories:

AICS : All ingredients listed or exempt.

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version 5.0	Revision Date: 10/17/2017	SDS Number: 838796-00009	Date of last issue: 05/02/2017 Date of first issue: 11/26/2014
----------------	------------------------------	-----------------------------	---

IECSC : All ingredients listed or exempt.

ENCS/ISHL : All components are listed on ENCS/ISHL or exempted from inventory listing.

TSCA : All chemical substances in this product are either listed on the TSCA Inventory or are in compliance with a TSCA Inventory exemption.

PICCS : All ingredients listed or exempt.


DSL : All chemical substances in this product comply with the CEPA 1999 and NSNR and are on or exempt from listing on the Canadian Domestic Substances List (DSL).

TCSI : All ingredients listed or exempt.

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS® IV:

HEALTH	/	0
FLAMMABILITY		1
PHYSICAL HAZARD		0

HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. The "*" represents a chronic hazard, while the "/" represents the absence of a chronic hazard.

Full text of other abbreviations

OSHA Z-3 : USA. Occupational Exposure Limits (OSHA) - Table Z-3 Mineral Dusts

OSHA Z-3 / TWA : 8-hour time weighted average

AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated

SAFETY DATA SHEET

MOLYKOTE™ 112 High Performance Lube/ Sealant



Version	Revision Date:	SDS Number:	Date of last issue: 05/02/2017
5.0	10/17/2017	838796-00009	Date of first issue: 11/26/2014

with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Sources of key data used to compile the Material Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Revision Date : 10/17/2017

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

US / Z8