




- NOTES:
- 1. SUBSTRATE:
POLYMER FILM
 - 2. POLARIZATION: > 88% EFFICIENCY
 - 3. TRANSMISSION:
SINGLE: 38
PARALLEL: 32
CROSSED: 0.75
 - 4. UV ABSORPTION: >88%
 - 5. OPERATING TEMPERATURE: -50 TO 70°C
 - 6. WAVELENGTH RANGE: 450 - 675 nm
 - 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®		
TITLE		8.5" x 5" Linear Polarizing Film		
ALL DIMS IN	mm	DWG NO	19291	SHEET 1 OF 1