




NOTES:

1. SUBSTRATE:  
CP42HE Laminated Between Glass
2. OPERATING TEMPERATURE: -40 to +80 °C
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: Uncoated
4. EFFICIENCY OF LINEAR COMPONENT: >99.90 %
5. WAVELENGTH RANGE: 400 - 700 nm
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**<sup>®</sup> Edmund Optics<sup>®</sup>

THIRD ANGLE PROJECTION 		TITLE	20mm Dia. Left-Handed Uncoated Glass Circular Polarizer (CP42HE)	
ALL DIMS IN	mm	DWG NO	19928	SHEET 1 OF 1