

NOTES:

- 1. SUBSTRATE: Suprasil® 300
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCSEC
- 3. COATING (APPLY ACROSS COATING APERTURE) \$1 & \$2: BBAR (1650-3000nm) R(AVG) <1% @ 1650 - 3000nm R(ABS) <2% @ 1650 - 3000nm
- 4. TRANSMITTED WAVEFRONT DISTORTION P-V: ≤ 0.10 WAVE @ 632.8nm

5. FINE GRIND SURFACE

6. ROHS COMPLIANT





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Ontion®

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	10-5	10-5	
WAVELENGTH RANGE	1650 - 3000nm	1650 - 3000nm	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

THIRD ANGLE PROJECTION		TITLE	20mm Dia., 2mm Thick, BBAR (1650-3000nm) Coated, Suprasil Window			
ALL DIMS IN	mm	DWG NO	21244	SHEET 1 OF 1		