NOTES:

1. SUBSTRATE: Fused Silica (Corning 7980)

2. ROHS: COMPLIANT


3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCMIN


4. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(ABS) ≤1.0% @ 250 - 425nm R(AVG) ≤0.75% @ 250 - 425nm R(AVG) ≤0.5% @ 370 - 420nm

5. TRANSMITTED WAVEFRONT DISTORTION: ≤ 1λ









FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 22.50	Ø 22.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION	$\phi \Leftrightarrow$	TITLI
ALL DIMS IN	mm	DW

B	Edmund Optics®
TITLE	25mm Dia., 3mm Thick UV-AR Coated, 1λ Fused Silica Window