
## NOTES:


- 1. SUBSTRATE: Fused Silica (Corning 7980)
- 2. ROHS: COMPLIANT
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN <5 ARCMIN
- 4. COATING (APPLY ACROSS CLEAR APERTURE)


\$1&\$2: R(AB\$) ≤1.0% @ 250 - 425nm R(AVG) ≤0.75% @ 250 - 425nm R(AVG) ≤0.5% @ 370 - 420nm

5. TRANSMITTED WAVEFRONT DISTORTION: ≤ 1λ









1 OF 1

## FOR INFORMATION ONLY: DO NOT MANUFACTURE **PARTS TO THIS DRAWING**

ALL DIMS IN

	51	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	60-40 60-4	60-40	
CLEAR APERTURE	Ø 45.00	Ø 45.00	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

			Eamuna Optic	;S <sup>®</sup>
THIRD ANGLE PROJECTION		TITLE	50mm Dia., 3mm Thick UV-AR Coated Fused Silica Window	d, 1λ
ALL DIMS IN	mm	DWG NO	10000	SHEET

19888

DWG NO

DIMENSIONS ARE FOR REFERENCE ONLY

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE