Collimated Backlights

PRODUCT DATA SHEET



BL-CL

The Collimated Backlight Series is a high performance, uniform, and collimated light source for high precision silhouetting and transmissive applications. Using precision optics, these lights are collimated in both the X and Y dimensions. The light exits at a low divergence angle making it perfect for applications requiring high precision measurements when used with a telecentric lens. Using a full array LED layout with more LEDs per square inch to provide greater intensity and uniformity. The Collimated Backlight Series is available with a wide variety of LED colors: White, Red, Green, Blue, IR, and RGB with independent color control. Active areas ranging from 1-inch x 1-inch (25 mm x 25mm) to 12 inches x 12 inches (305 mm x 305 mm). Custom sizes up to 3 feet x 3 feet (1 m x 1 m) are available.



FEATURES

- High density LED array makes our backlights the brightest and most stable backlights
- Exclusive optical lens provides high uniformity (±5%), shadow-free backlight illumination
- Thermal management design draws heat directly from the die ensuring long life
- Available in large custom sizes and in square and rectangular footprints
- Flicker free performance and instant start up with Metaphase analog driver technology
- Optional Constant Current driver with 0-10VDC intensity control (-Z option)

WAVELENGTHS						
Order ID Description / nanometers						
W	White (6000K), Nominal					
R	Red 630nm					
G	Green 530nm					
В	Blue 470nm					
IR850 (or IRN)	Infrared 850nm*					
RGB	Red/Green/Blue (limited sizes)					

^{*}For other IR wavelengths, see our SWIR Backlights

GENERAL SPECIFICATIONS

Power Source: 24VDC ±5%

Cable (Standard): 10-foot cable with flying leads Housing: Black Anodized Aluminum

Ambient Temp: -20°C to 40°C **Lifetime Expectancy:** 75,000 hours

Glass Cover: Surface Quality 80/50 scratch/dig or

better

Collimated Backlights

PRODUCT DATA SHEET



BL-CL

Collimated Backlights										
	Width and				QTY	Cable Length	Wires	Maximum Input Current (Amps)		
MODEL*	Length Inches (cm)	Height Inches (cm)	Active Area Inches (cm)	Weight lbs (kg)	Cable (Cable I	AWG/ Wires	Visible	IR	
BL1x1-CL	2.75 x 2.75 (6.985 x 6.985)	.93 (2.356)	.93 x .93 (2.357 x 2.357)	.22 (.010)				.15	.20	
BL2x2-CL	3.75 x 3.75 (9.525 x 9.525)	.938 (2.383)	2.03 x 2.03 (5.166 x 5.166)	.40 (.181)			24/4	.50	.70	
BL2x4-CL	3.75 x 5.75 (9.525 x 14.60)	.938 (2.383)	2.02 x 4.02 (5.141 x 10.22)	.70 (.318)				.85	1.1	
BL3x3-CL	4.35 x 4.50 (11.05 x 11.43)	.938 (2.383)	3.09 x 3.09 (7.849 x 7.856)	.79 (.358)			ŕ	.85	1.1	
BL3x4-CL	4.50 x 5.35 (11.43 x 13.59) 5.41 x 6.38	.938 (2.383) 1.67	3.09 x 4.09 (7.856 x 103.9) 4.0 x 4.0	.82 (.372) 1.3	1	10ft		1.0	1.4	
BL4x4-CL	(12.88 x 12.88) 6.41 x 7.38	(4.24 1.67	(10.16 x 10.16) 5.0 x 5.0	(.590)	_			1.2	1.6	
BL5x5-CL	(16.28 x 18.75) 7.75 x 13.75	(4.24)	(12.70 x 12.70) 5.91 x 11.91	(.907) 3.6				1.4	1.9	
BL6x12-CL	(19.68 x 34.92) 13.75 x 13.75	(2.383)	(15.01 x 30.25) 11.91 x 11.91	(1.63)	-		18/4	2.2	3.4	
BL12x12-CL	(34.92 x 34.92)	(2.383)	(30.25 x 30.25) Unique Configu	(2.27)				4.5	6.0	
BL3x3-CL-9D	4.35 x 4.50 .938 3.09 x 3.09 .79 D-Sub connector,				.85	1.1				
BL3x3-CL-RGB	4.35 x 4.50 (11.05 x 11.43)	1.410 (3.581)	3.09 x 3.09 (7.849 x 7.856)	.84 (.381)	D-Sub connector, 9P (male) [RGB] 1.0] 1.0		

^{*}Custom sizes available

PRODUCT DATA SHEET



BL-CL

Wiring (4 conductors, flying leads)**						
Wire Color	Function					
RED	+24VDC					
WHITE	0-10VDC INTENSITY CONTROL					
BLACK	GROUND (24V RTN)					
GREEN	SIGNAL GROUND					

Wiring (4 conductors, without Intensity Control)					
Wire Color	Function				
RED	+24VDC				
WHITE	+24VDC				
BLACK	GROUND (24V RTN)				
GREEN	GROUND (24V RTN)				

M12 (5 position male)**						
Pin #	Function					
1	+24VDC					
2	0-10VDC Intensity Control					
3	GROUND (24V RTN)					
4	SIGNAL GROUND					
5	No Connection					
The M12 connector option is not recommended for lights rated						

The M12 connector option is not recommended for lights rated more than 4 amps

Wiring with ULC-2					
Wire Color	Function				
RED, WHITE (+)	LED INPUT				
BLACK, GREEN (-)					
Terminated within a 2 position ULC-2 output connector (Phoenix Contact P/N: BCP-508-2)					

^{**}Note: The 0-10VDC Intensity Control input can accept voltages from 0-24VDC where the light will operate at full intensity in the 10-24VDC range. The light is proportionally dimmer for any Intensity Control voltage less than 10VDC and the light is OFF at approximately 0V or not connected (floating).

Wiring (9P D-Sub connector) *						
Position #	Function					
1	+24VDC					
2	+24VDC					
3	+24VDC					
4	Positive Sense Line					
5	Negative Sense Line					
6	GROUND (24V RTN)					
7	GROUND (24V RTN)					
8	GROUND (24V RTN)					
9	GROUND (24V RTN)					

^{*}Example pin assignment

Collimated Backlights

PRODUCT DATA SHEET



BL-CL

MODEL NUMBER KEY						
MODEL	-	WAVELENGTH		OPTION 1		OPTION 2
BLXxX-CL	-	XXX	-	XXX	-	X-XXX
BL1X1-CL		W (White 6000K, Nominal)		24 (+24VDC, standard)		Z (0-10V Intensity Control)
BL2X2-CL		R (Red 630nm)				
BL2X4-CL		G (Green 530nm)				
BL3X3-CL		B (Blue 470nm)				
BL3X4-CL		IR850 (or IRN) (Infrared 850nm)				
BL4X4-CL						T (M12 Connector)
BL5X5-CL						
BL6X12-CL				U (ULC-2 interface)		
BL12X12-CL				KEY (Keyence Controller)		
BL3X3-CL-9D				ILD (In Line Dimmer)		
BL3X3-CL-RGB				ILS (In Line Strobe)		XXX (Custom code)


Contact Metaphase Technologies or your local representative for options such as custom diffusers, lenses, polarizers, IP-rated enclosures for harsh environments, higher intensity, custom wavelengths, higher uniformity, etc. Not all options are available for all lights.

PRODUCT DATA SHEET



BL-CL

Sample Model Number: BL3x3-CL-W-24-Z



COMPLIANCE





CONTACT US

Contact Metaphase Technologies at **215-639-8699** or your local representative for additional details, options and customizations.